

# YGIBW346132N

by Burndy  
Catalog ID: YGIBW346132N

Prop 65 Notice

I-Beam Connector for Copper Cable, 2 AWG - 500 kcmil, i-Beam flange  
Thickness: .550 IN to .613 IN



## Product Details

### General

Connector Type	Tap
I Beam Style	Wide Flange Beam (Flange Parallel)
Material	Copper
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810039410
UPC 12 Digit	7818100394100

### Dimensions

Dimension - B Length fraction	6 in
Dimension - B Length inch	6.00 in
Dimension - I Beam Thickness Range inch	0.501;0.525;0.550;0.562
Dimension - I Beam Thickness inch	0.550" - 0.613""
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

### Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL467</li> <li>IEEE 837</li> </ul>

Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL467</li><li>• IEEE 837</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)