

YGS34

by Burndy
Catalog ID: YGS34

Prop 65 Notice

Grounding IrreversibleCompression Splices.



Product Details

General

Connector Type	Splice
Die Index	20
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810220443
UPC 12 Digit	7818102204433

Dimensions

Dimension - B Length fraction	2-1/5 in
Dimension - B Length inch	2.20 in
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.63 in
Dimension - Outside Diameter inch	1.06 in

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	- UL467 - UL 486A-486B

Standards - Industry Standards Met	• UL 486A-486B • UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)