



## YH4444WC

by Burndy  
Catalog ID: YH4444WC

Prop 65 Notice

Cu H-Tap Crimpit W/Black Cover Kit, 1000-750(Main), 1000-750(Tap), Tin Plated, White.

Features: Accommodates A Wide Range Of Run/Tap Copper Cable Combinations Including Both Flexible And Code Combinations, All (B/B, B/I, I/B, I/I) Combinations Acceptable: Each Connector Has Many Copper Cable Combination Applications Allowing Maximum Flexibility For The Design And Installation Of A System, Tap Grooves Function Independently Of Each Other, Use Of One Tap Is Required, Balance May Be Used Or Left Empty: Provides Maximum Design And Installation Flexibility, Color Code On The Connector Matches Installation Die: Provides Matched System For Fast And Easy Installation, Die Index Embossed On Connector After Completion Of Crimp: Permanent Inspectability Of Installed Connectors To Insure Consistently Reliable And Dependable Connections, Recommended Flame Retardant Type CFFR Insulating Covers Meet Oxygen Index 28 And UL94 V-O Requirements: A Complete Insulated UL Listed Installation Is Provided, Third Hand Constrains Conductors While Installer Completes Crimp, Included With Each Connector, Simplifies Installation, Reducing Installed Cost, Tools, Die Set Catalog Number, And (number Of Crimps): Y46 Tool, P1102 Die, (1), Wire Strip Length: 1-1/8 IN, Color Code: White, Flame Retardant Cover: CFR-FR, Die Index: 1102 Element A, Cover Packaged With Connector: Yes, Conductor Size (run - Range): 500 - 1000 KCMIL, Conductor Type: Run: Commercial Stranded Copper, Flexible Copper, Tap: Commercial Stranded Copper, Flexible Copper, Conductor Size (tap Range): 350 - 1000 KCMIL, Shape: H

## Product Details

### General

Application	For Used To Accommodates A Wide Range Of Run/Tap Copper Cable Combinations Including Both Flexible And Code Combinations
Color Code	White
Connector Type	H-Tap
Die Index	1102
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Type	Compression Taps
UPC	781810000342
UPC 12 Digit	7818100003422

### Dimensions

Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1-1/8
Dimension - Width inch	3.38 in

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper Flex G Run	500;600;700
Conductor - Copper Flex G Tap	500;600;700
Conductor - Copper Flex H Tap	500;600;700
Conductor - Copper Flex I Run	500;550;600;700
Conductor - Copper Flex I Tap	500;550;600;700
Conductor - Copper Flex K Run	500;600;700
Conductor - Copper Flex K Tap	500;600;700
Conductor - Copper Flex M Run	500;600;700
Conductor - Copper Flex M Tap	500;600;700
Conductor - Copper Str Run	700;750;800;850;900;1000
Conductor - Copper Str Tap	750;800;850;900;1000

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)