




YH4444

by Burndy
Catalog ID: YH4444

Prop 65 Notice

Copper Compression H Tap, 1000-750 kcmil (Main), 1000-750 kcmil (Tap), Tin Plated

Product Details

General

Color Code	White
Connector Type	H-Tap
Die Index	1102
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Compression Taps
UPC	781810013854
UPC 12 Digit	7818100138544

Dimensions

Dimension - Height inch	3.38 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	1 in
Dimension - Strip Length inch	1-1/8
Dimension - Width fraction	1.70 in
Dimension - Width inch	3.38 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Run	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex G Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex G Tap	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex G Tap Range	500 kcmil-700 kcmil
Conductor - Copper Flex H Run	700 kcmil
Conductor - Copper Flex H Run Range	700 kcmil

Conductor - Copper Flex H Tap	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex H Tap Range	500 kcmil-700 kcmil
Conductor - Copper Flex I Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex I Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex I Tap	500 kcmil;550 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex I Tap Range	500 kcmil-700 kcmil
Conductor - Copper Flex K Run	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex K Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex K Tap	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex K Tap Range	500 kcmil-700 kcmil
Conductor - Copper Flex M Run	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex M Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex M Tap	500 kcmil;600 kcmil;700 kcmil
Conductor - Copper Flex M Tap Range	500 kcmil-700 kcmil
Conductor - Copper Str Run	700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	700 kcmil-1000 kcmil
Conductor - Copper Str Tap	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	750 kcmil-1000 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)