

YHD350

by Burndy
Catalog ID: YHD350



Compression Line Tap for Copper, AL or ACSR and Compact Conductors, wire diameter range, groove A(Run):0.461-0.563.

Features: Wide Range, Universal And Reversible Figure H Shaped Aluminum Connector, Conductors Are Separated By The Shape Of The Connector, Bendable Tabs Secure Both Run And Tap Conductors Freeing The Linemans Hands To Work With The Installation Tool, Massive Aluminum Design Minimizes Corrosion Due To Galvanic Corrosion, Prefilled With PENETROX Joint Compound And Individually Packaged, Conductor Ranges And Tooling Clearly Printed On Connector And Package, Cable Diameter Range (run): 0.461 - 0.563 IN, Cable Diameter Range (tap): 0.338 - 0.447 IN, Shape: H, Conductor Type: Run: ACSR, Tap: ACSR, Die Index: D3 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6-8, MD7-8 Tool, (7), Y35, Y750 Tool, UD3 Die, (2), Y45 Tool, UD3 Die With PT-6515 Adapter, (2), Y46 Tool, UD3 Die With PUADP-1 Adapter, (2)

Product Details

General

Application	For Copper, Aluminum Or ACSR And Compact Conductors
Die Index	D3
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYCRIMP
Trade Name	HYCRIMP™
Type	YHD
UPC	781810139301

Dimensions

Dimension - Height fraction	1-21/50 in
Dimension - Height inch	1.42 in
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.25 in
Dimension - Width fraction	89/100 in
Dimension - Width inch	0.89 in
Dimension - Width mm	23 mm

Conductor Related

Conductor - ACSR Cmpt Run	1/0 AWG;2/0 AWG
Conductor - ACSR Cmpt Run Range	1/0 AWG-2/0 AWG
Conductor - ACSR Cmpt Tap	1 AWG;1/0 AWG;3/0 AWG;2/0 AWG
Conductor - ACSR Cmpt Tap Range	1 AWG-2/0 AWG
Conductor - ACSR Str Run	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG

Conductor - ACSR Str Run Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Tap Range	1 (6/1) Robin AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Run	3/0-4/0
Conductor - AL Str Run Range	3/0-4/0
Conductor - AL Str Tap	2/0 AWG;3/0 AWG
Conductor - AL Str Tap Range	2/0 AWG-3/0 AWG
Conductor - Copper Solid Run	250 - 300
Conductor - Copper Solid Run Range	250 - 300
Conductor - Copper Solid Tap	2/0 AWG;3/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Run	3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Tap	1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	1 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)