

YKA30R2N

by Burndy
Catalog ID: YKA30R2N

Prop 65 Notice

Al Compression terminal, 266.8(.609)(.633), 317"L, 317 or 705 index.

Features: Aluminum Compression Terminal With Fixed Hardware And Positioning Pin For Making Disconnectable Tap Or Jumper Connections, Used With Slotted YTA-R-2N T-Tap Or YSA-R-2N Terminal, Supplied With Aluminum Bolts And Washer-Face, Self Locking Nuts, Prefilled With PENETROX Joint Compound And Capped, Pad Configuration: Straight, Size: 7-1/4 IN Overall Length X 3/8 IN Pad Thickness X 1-7/8 IN Pad Width X 3 IN Pad Length, Die Index: 317 Or M, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-M Die, (3), U317 Die, (4), Wire Type: ACSR 6201 5005 (Compressed / Compact), Aluminum, Copper



Product Details

General

Application	For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors And Making Disconnectable Tap Or Jumper Connections
Connector Type	Terminal
Die Index	M;317
Material	Aluminum
Physical Attribute - Pad Configuration	Straight
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Type	YKA-R-2N, Disconnectable
UPC	781810017012

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.90 in

Conductor Related

Conductor - ACSR Str Size	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - AL Str Size	250 kcmil;266 kcmil
Conductor - Copper Str Size	250 kcmil;300 kcmil
Conductor - Copper Str Size Range	250 kcmil-300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)