



YNA32R45

by Burndy
Catalog ID: YNA32R45

Prop 65 Notice

Aluminum Compression Terminal 230 kV, 300-336.4 kcmil ACSR, 336.4-350 kcmil Alum., 395.1-395.2 kcmil ACAR, 45 Deg

Product Details

General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Pad Orientation	45 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810283905
UPC 12 Digit	7818102839055

Dimensions

Dimension - B Length inch	4.18 in
Dimension - Height fraction	5-3/20 in
Dimension - Height inch	5.15 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in

Conductor Related

Conductor - ACAR Str Size	400 (19)
Conductor - ACAR Str Size Range	400 (19)
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich-336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350
Conductor - AL Str Size Range	336.4-350

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)