

YNA32R90

by Burndy
Catalog ID: YNA32R90

Prop 65 Notice

HYLUG™, Aluminum Tube Compression Terminal operates at 345 Kv,
300-336.4 Kcmil ACSR, 336.4-350 Kcmil Al, 395.1-395.5 Kcmil, 90 Deg



Product Details

General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Pad Orientation	90 Degree
Prefilled Oxide Inhibitor	Y
UPC	781810093429
UPC 12 Digit	7818100934299

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Height fraction	6-11/20 in
Dimension - Height inch	6.55 in
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.65 in
Dimension - Outside Diameter inch	1.19 in

Conductor Related

Conductor - ACAR Str Size	395.1;395.2
Conductor - ACAR Str Size Range	395.1;395.2
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich-336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350
Conductor - AL Str Size Range	336.4-350

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)