



YNA39R

by Burndy
Catalog ID: YNA39R

Prop 65 Notice

Compression Terminal for ACSR Conductor, 634.9-653.1 ACAR 600-650 Alum.556.5 ACSR, 4 Pad holes, 9-3/4 in Length.

Features:Compression Terminal for ACSR Conductor

Product Details

General

Application	For use on: ACSR, ACAR and SAC Transmission Lines
Connector Type	Terminal
Die Index	722
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YNS-R
UPC	781810016343
UPC 12 Digit	7818100163433

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	250 mm
Dimension - Length Overall inch	9.84 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.08 in
Dimension - Width fraction	2.08 in

Conductor Related

Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil
Conductor - AL Str Size	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)