



YNA52RT

by Burndy
Catalog ID: YNA52RT

Prop 65 Notice

HYLUG™, Aluminum Tube Compression Terminal, 4 Holes, 1113.54-19 Str Kcmil ACSR, 1351.5 - 1510 Kcmil Al, 1277 - 1280 Kcmil ACAR, greater than 230 kV, 1.75" Spacing

Product Details

General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016381
UPC 12 Digit	7818100163811

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	351 mm
Dimension - Length Overall inch	13.82 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

Conductor Related

Conductor - ACAR Str Size	1277 KCMIL- 1280 KCMIL
Conductor - ACAR Str Size Range	1277 KCMIL- 1280 KCMIL
Conductor - ACSR Str Size	1113 (54/19) Finch
Conductor - ACSR Str Size Range	1113 (54/19) Finch
Conductor - AL Str Size	1351.5;1400;1431.0;1500
Conductor - AL Str Size Range	1351.5-1500

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)