



YNA56RT15H

by Burndy
Catalog ID: YNA56RT15H

Prop 65 Notice

HYLUG™, Al Compression Terminal, 1510.5-1590 Kcmil ACSR, 1700-1800 Kcmil Aluminum, 1650 Kcmil ACAR, 4 Pad Holes, 345 Kv, Extra High Voltage Applications, 15 Degree including hardware

Product Details

General

Connector Type	Terminal
Die Index	729
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810222911
UPC 12 Digit	7818102229111

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	339 mm
Dimension - Length Overall inch	13.36 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.44 in
Dimension - Width fraction	3.44 in

Conductor Related

Conductor - ACAR Str Size	1650 KCMIL
Conductor - ACAR Str Size Range	1650 KCMIL
Conductor - ACSR Str Size	1590 (54/19) Falcon
Conductor - ACSR Str Size Range	1590 (54/19) Falcon
Conductor - AL Str Size	1700 KCMIL -1800 KCMIL
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)