

# YNA585RT

by Burndy  
Catalog ID: YNA585RT

Prop 65 Notice

HYLUG™, Al Tube Compression Terminal, operates 345 Kv, 2032.5-2034.5 Kcmil ACSR, Cable to flat, Extra high voltage applications



## Product Details

### General

|                                      |               |
|--------------------------------------|---------------|
| Connector Type                       | Terminal      |
| Die Index                            | 735           |
| Material                             | Aluminum      |
| Physical Attribute - Pad Orientation | Straight      |
| Prefilled Oxide Inhibitor            | Y             |
| Trade Name                           | HYLUG™        |
| UPC                                  | 781810221907  |
| UPC 12 Digit                         | 7818102219077 |

### Dimensions

|  |          |
|--|----------|
| Dimension - Bolt Hole Size inch              | 0.56 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm              | 350 mm   |
| Dimension - Length Overall inch              | 13.79 in |
| Dimension - Outside Diameter inch            | 2.5 in   |
| Dimension - Pad Width inch                   | 3.5 in   |
| Dimension - Width fraction                   | 3.50 in  |

### Conductor Related

|                                 |               |
|---------------------------------|---------------|
| Conductor - ACSR Str Size       | 2032.1;2034.5 |
| Conductor - ACSR Str Size Range | 2032.1-2034.5 |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 125 |
|-----------------------|-----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)