



## YNA59R

by Burndy  
Catalog ID: YNA59R

Prop 65 Notice

HYLUG™, Aluminum Compression terminal for ACSR, Aluminum, ACAR transmission lines, 2156-2167 Kcmil ACSR, 2250-2300 Kcmil Aluminum, Tube to flat, 4 Pad holes

## Product Details

### General

Connector Type	Terminal
Die Index	735
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810460528
UPC 12 Digit	7818104605288

### Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	337 mm
Dimension - Length Overall inch	13.25 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.57 in
Dimension - Width fraction	3.57 in

### Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 kcmil;2300 kcmil
Conductor - AL Str Size Range	2250 kcmil;2300 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)