



YNA7M9T

by Burndy
Catalog ID: YNA7M9T

Prop 65 Notice

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #9, 3 #6 Alumoweld

Product Details

General

Connector Type	Terminal
Die Index	677
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810081549
UPC 12 Digit	7818100815499

Dimensions

Dimension - B Length inch	2.79 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	223 mm
Dimension - Length Overall inch	8.79 in
Dimension - Outside Diameter inch	0.8 in
Dimension - Pad Width inch	1.5 in

Conductor Related

Conductor Type	GAL Steel C Str-Size
----------------	----------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)