



YNS43R

by Burndy Catalog ID: YNS43R

Prop 65 Notice

HYSPLICE™ Jumper Loop Sleeve, Al Tube, 605 - 666.6 kcmil ACSR, 700 - 800 kcmil Al, 230 kV, 9.98" L, 724 Index

Product Details

General

Connector Type	Splice
Die Index	724
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016121
UPC 12 Digit	7818100161211

Dimensions

Dimension - L Length Overall mm	253 mm
Dimension - Length Overall inch	9.98 in
Dimension - Outside Diameter inch	1.61 in

Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109 **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)