

# YNS54R

by Burndy  
Catalog ID: YNS54R

Prop 65 Notice

HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 1534 Kcmil ACAR, 1590-1600 Kcmil AL, 1431 Kcmil ACSR



## Product Details

### General

Connector Type	Splice
Die Index	728
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810180648
UPC 12 Digit	7818101806488

### Dimensions

Dimension - L Length Overall mm	393 mm
Dimension - Length Overall inch	15.48 in
Dimension - Outside Diameter inch	2.25 in

### Conductor Related

Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - ACSR Str Size	1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1431 (54/19) Plover kcmil
Conductor - AL Str Size	1590 KCMIL - 1600 KCMIL
Conductor - AL Str Size Range	1590 KCMIL - 1600 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)