

# YNT49R49R

by Burndy  
Catalog ID: YNT49R49R

Prop 65 Notice

Aluminum Compression Two piece T-Tap connector, 230 kV, 1033.5-1272 kcmil Aluminum, 2 Pad holes



## Product Details

### General

Connector Type	Tap
Die Index	727
Material	Aluminum
UPC	781810116562
UPC 12 Digit	7818101165622

### Dimensions

Dimension - Height fraction	7-3/4 in
Dimension - Height inch	7.75
Dimension - Length Overall inch	17.50

### Electrical Ratings

Voltage Rating	230 kV
----------------	--------

### Conductor Related

Conductor - ACAR Str Run Range	983.1 kcmil -1198 kcmil
Conductor - ACAR Str Tap Range	983.1 kcmil -1198 kcmil
Conductor - ACSR Str Run Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - ACSR Str Tap Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - AL Str Run Range	1033.5 kcmil-1272 kcmil
Conductor - AL Str Tap Range	1033.5 kcmil-1272 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)