

YNT56R56RT

by Burndy
Catalog ID: YNT56R56RT

Prop 65 Notice

Two-piece aluminum compression T-Tap connector, 1510.5-1590 Kcmil ACSR, 1700-1800 Kcmil Aluminum, Tube to tube, 729 Index



Product Details

General

Connector Type	Tap
Die Index	729
Material	Aluminum
UPC	781810253878
UPC 12 Digit	7818102538788

Dimensions

Dimension - B Length inch	6.94 in
Dimension - Height fraction	11-2/25 in
Dimension - Height inch	11.08 in
Dimension - Length Overall inch	23.65 in
Dimension - Outside Diameter inch	2.5 in

Conductor Related

Conductor - ACAR Str Run	1650
Conductor - ACAR Str Run Range	1650
Conductor - ACAR Str Tap	1650
Conductor - ACAR Str Tap Range	1650
Conductor - ACSR Str Run	1590 (54/19) Falcon
Conductor - ACSR Str Run Range	1590 (54/19) Falcon
Conductor - ACSR Str Tap	1590 (54/19) Falcon
Conductor - ACSR Str Tap Range	1590 (54/19) Falcon
Conductor - AL Str Run	1700;1750;1800
Conductor - AL Str Run Range	1700-1800
Conductor - AL Str Tap	1700;1750;1800
Conductor - AL Str Tap Range	1700-1800

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)