

YNTA451R

by Burndy
Catalog ID: YNTA451R

Prop 65 Notice

Al Terminal Tee-Taps (Extruded) With Pad, 4 Holes, 715.5 - 874.5 Kcmil
ACSR, 795 - 1000 Kcmil Al, 230 kV, 1.75" Spacing



Product Details

General

Connector Type	Tap
Die Index	725
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810016572
UPC 12 Digit	7818100165722

Dimensions

Dimension - B Length inch	4.56 in
Dimension - Height fraction	5-11/20 in
Dimension - Height inch	5.55 in
Dimension - Length Overall inch	17.60 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.25 in

Conductor Related

Conductor - ACAR Str Size	800 (37);850 (37);900 (37);950 (37)
Conductor - ACAR Str Size Range	800 (37)-950 (37)
Conductor - ACSR Str Size	715.5 (26/7) Kcmil;795 (24/7) Kcmil;795 (26/7) Kcmil;795 (45/7) Kcmil;795 (54/7) Kcmil
Conductor - ACSR Str Size Range	715.5 - 874.5 Kcmil
Conductor - AL Str Size	795.5;800;874.5;900;954;1000
Conductor - AL Str Size Range	795.5-1000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)