

YNTA49R

by Burndy
Catalog ID: YNTA49R

Prop 65 Notice

Al Terminal Tee-Taps (Extruded) With Pad, 4 Holes, 900 - 1113 Kcmil
ACSR, 1033.5 - 1272 Kcmil Al, 230 kV, 1.75" Spacing



Product Details

General

Connector Type	Tap
Die Index	727
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810016510
UPC 12 Digit	7818100165100

Dimensions

Dimension - B Length inch	4.57 in
Dimension - Height fraction	5-18/25 in
Dimension - Height inch	5.72 in
Dimension - Length Overall inch	17.66 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.25 in

Conductor Related

Conductor - ACSR Str Size	900 (45/7) Kcmil;954 (45/7) Kcmil;954 (54/7) Kcmil;1033.5 (45/7) Kcmil;1033.5 (54/7) Kcmil;1113 (45/7) Kcmil
Conductor - ACSR Str Size Range	900 (45/7) Kcmil-1113 (45/7) Kcmil
Conductor - AL Str Size Range	1033.5 kcmil - 1272.2 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)