



YNTA594R

by Burndy
Catalog ID: YNTA594R

Prop 65 Notice

T-TAP WITH PAD TAP.

Product Details

General

Connector Type	Tap
Die Index	740
Material	Aluminum
UPC	781810180846
UPC 12 Digit	7818101808466

Dimensions

Dimension - B Length inch	7.6 in
Dimension - Height fraction	6-7/20 in
Dimension - Height inch	6.35 in
Dimension - L Length Overall mm	617 mm
Dimension - Length Overall inch	24.30 in
Dimension - Outside Diameter inch	2.6 in
Dimension - Pad Width inch	3.59 in
Thickness - Pad	0.69 in

Conductor Related

Conductor - ACAR Str Size	2267 Kcmil; 2500 Kcmil
Conductor - ACAR Str Size Range	2267 Kcmil - 2500 Kcmil
Conductor - ACSR Str Size	2300 Kcmil
Conductor - AL Str Size	2500 Kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)