

YNU43R

by Burndy
Catalog ID: YNU43R

Prop 65 Notice

Al Repair Sleeve, 605 - 666.6 kcmil ACSR, 700 - 800 kcmil Al, 16.00" L, 724 Index



Product Details

General

Connector Type	Splice
Die Index	724
Material	Aluminum
UPC	781810016527
UPC 12 Digit	7818100165277

Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Dimension - Outside Diameter inch	1.61 in

Conductor Related

Conductor - ACSR Str Size	605 (24/7) kcmil;605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;666.6 (24/7) kcmil
Conductor - ACSR Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)