

YOT3434

by Burndy
Catalog ID: YOT3434

Cast copper T-tap connector with two-piece line element and tubular tap for joining hard and medium drawn copper. Design simplifies installation on large conductors.



Product Details

General

Connector Type	Tap
Die Index	210
Die Index Run Side	210
Die Index Tap Side	210
Material	Copper
UPC	781810014714

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Height fraction	4-8/10
Dimension - Height inch	4.82 in
Dimension - L Length Overall mm	264 mm
Dimension - Length BB inch	2.5 in
Dimension - Length Overall inch	10.38 in
Dimension - Outside Diameter inch	1.4 in
Dimension - Width fraction	1-23/25 in
Dimension - Width inch	1.92 in
Dimension - Width mm	49 mm

Conductor Related

Conductor - Copper Str Run	500 kcmil
Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap	500 kcmil
Conductor - Copper Str Tap Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)