

YOU32R

by Burndy
Catalog ID: YOU32R

Prop 65 Notice

Cast Aluminium Repair Sleeve, 300 (26-7) kcmil, 13 IN L, 316 Index



Product Details

General

Connector Type	Splice
Die Index	316
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810016046
UPC 12 Digit	7818100160466

Dimensions

Dimension - L Length Overall mm	329 mm
Dimension - Length Overall inch	12.94 in

Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil
Conductor - AL Str Size	300 kcmil
Conductor - AL Str Size Range	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)