

YPC28R28A

by Burndy
Catalog ID: YPC28R28A

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:3/0 - 4/0 & 4/0, 266.8 (18/1) ACSR Compressed



Product Details

General

Die Index	D3
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810137451
UPC 12 Digit	7818101374511

Dimensions

Dimension - Height inch	1.70 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in

Conductor Related

Conductor - ACSR Str Run	3/0 AWG, 4/0 AWG
Conductor - ACSR Str Run Range	3/0 AWG-4/0 AWG
Conductor - AL Str Run	3/0 AWG, 4/0 AWG
Conductor - AL Str Run Range	3/0 AWG-4/0 AWG
Conductor - AL Str Tap	3/0 AWG, 4/0 AWG
Conductor - AL Str Tap Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Run	3/0 AWG; 4/0 AWG
Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Tap	3/0 AWG; 4/0 AWG
Conductor - Copper Str Tap Range	3/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)