



YPC2A8U

by Burndy Catalog ID: YPC2A8U

Compact compression connector designed to tap small lighting wires from secondaries. Figure 6-shape separates run and tap, and minimizes galvanic corrosion.

Features: Compact Compression Connector Designed To Tap Small Lighting Wires From Secondaries, Figure 6 -Shape Separates Run And Tap, And Minimizes Galvanic Corrosion, Connector Can Be Gripped In Tool And Slipped Over Line For Easier Installation, Pre-Filled With PENETROX Joint Compound And Stripsealed, Conductor Type: ACSR, Compressed ACSR, Aluminum And Copper, Compressed Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-BG Die, (1), BG Die, (2), Y35, Y750 Tool, U-BG Die, (1), Y45 Tool, U-BG Die With PT-6515 Adapter, (1), Y46 Tool, U-BG Die With PUADP-1 Adapter, (1), OUR840 Tool, XBG Die, Die Index: BG Or 5/8 Element A, Shape: 6

Product Details

General	
Application	For Combinations Of Copper, Aluminum, ACSR, Compressed And Compact Conductors
Die Index	BG or 5/8
Plated	Ν
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Туре	YPC-A-U
UPC	781810135686
UPC 12 Digit	7818101356866

Dimensions

Dimension - Height inch	0.97 in
Dimension - L Length Overall mm	18 mm
Dimension - Length Overall inch	0.69 in
Dimension - Width inch	0.56 in

Conductor Related

Conductor - ACSR Str Run	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - AL Str Run	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Tap	8 AWG
Conductor - Copper Solid Run	4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Run Range	4 AWG-2 AWG
Conductor - Copper Solid Tap	14 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG

Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	14 AWG-8 AWG
Conductor Type	 AL C Str-Run CU C Str-Run CU C Solid-Run ACSR C Str-Run AL C Str-Tap CU C Str-Tap CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No	
Certification - ETL	No	
Certification - UL Recognized	No	
Certification - cULus	No	
Standards - RoHS Compliance Status	СМ	
UL Listed	No	
Logistics		

1

Minimum Pack Quantity

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)