

YPC33R28R



by Burndy
Catalog ID: YPC33R28R

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu: 250 (37) - 477 (37)

Features: Extra Wide Range Universal Connector, Two Dies And 5 Connectors Take Run Sizes 1/0- 600 KCMIL, And Tap Sizes 6-400 KCMIL, Wide Range Made Possible By Long Ram Travel Of BURNDY HYPRESS Tools, Figure 6- Shape Separates Run And Tap Wires, And Minimizes Galvanic Corrosion Of Conductors, Connector Can Be Gripped In Tool And Slipped Over Line For Easy Installation, Pre-Filled With PENETROX Joint Compound And Stripsealed, Conductor Type: ACSR, 5005, Aluminum And Copper, Shape: 6, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-N Die, (3), Y45 Tool, S-N Die, (3), Y46 Tool, P-N Die, (3), Die Index: N Element A

Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors
Construction Material - Main	Aluminum
Die Index	N
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810138007
UPC 12 Digit	7818101380077

Dimensions

Dimension - Height inch	2.28 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.88 in
Dimension - Width inch	1.16 in

Conductor Related

Conductor - ACSR Str Run Range	266.8 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	2/0 AWG-4/0 AWG
Conductor - AL Str Run	250 kcmil; 266 kcmil; 300 kcmil; 336 kcmil; 350 kcmil; 397 kcmil; 400 kcmil; 450 kcmil; 477 kcmil
Conductor - AL Str Run Range	250 kcmil-477 kcmil
Conductor - AL Str Tap	2/0 AWG; 3/0 AWG; 4/0 AWG
Conductor - AL Str Tap Range	2/0 AWG-4/0 AWG

Conductor - Copper Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil
Conductor - Copper Str Run Range	250 kcmil-477 kcmil
Conductor - Copper Str Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)