

# YPC36A32

by Burndy  
Catalog ID: YPC36A32

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:336.5 (26-7) - 556.5 (18-1)



## Product Details

### General

|              |               |
|--------------|---------------|
| Die Index    | Z             |
| Material     | Aluminum      |
| Plated       | N             |
| Plating Type | Unplated      |
| Trade Name   | CRIMPIT™      |
| UPC          | 781810138557  |
| UPC 12 Digit | 7818101385577 |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 3.70 in |
| Dimension - L Length Overall mm | 127 mm  |
| Dimension - Length Overall inch | 5 in    |
| Dimension - Width inch          | 2.00 in |

### Conductor Related

|                                  |  |
|----------------------------------|--|
| Conductor - ACSR Str Run Range   | 336.4 kcmil-556.5 kcmil  |
| Conductor - ACSR Str Tap Range   | 2/0 AWG- 397.5 kcmil   |
| Conductor - AL Str Run           | 397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil  |
| Conductor - AL Str Run Range     | 397 kcmil-600 kcmil  |
| Conductor - AL Str Tap           | 2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil  |
| Conductor - AL Str Tap Range     | 2/0 AWG-400 kcmil  |
| Conductor - Copper Str Run       | 397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil  |
| Conductor - Copper Str Run Range | 397 kcmil-600 kcmil  |
| Conductor - Copper Str Tap       | 2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil  |
| Conductor - Copper Str Tap Range | 2/0 AWG-400 kcmil  |
| Conductor Type                   | <ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• CU C Solid-Run</li> <li>• ACSR C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> <li>• CU C Solid-Tap</li> <li>• ACSR C Str-Tap</li> </ul> |

## Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)