



YRAL4CU

by Burndy
Catalog ID: YRAL4CU

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, Thickness: .25 IN

Product Details

General

Die Index	249;K-840
Material	Aluminum
Physical Attribute - Pad Configuration	1 Hole
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810088104
UPC 12 Digit	7818100881044

Dimensions

Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	1.43 in
Dimension - D inch	1.28 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.91 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.25 in

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size	2 AWG, 4 AWG
Conductor - AL Str Size Range	4 AWG-2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Size	2 AWG, 4 AWG

Conductor - Copper Str Size Range	2 AWG-4 AWG
-----------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)