

# YRB1CU2TTN

by Burndy  
Catalog ID: YRB1CU2TTN

Prop 65 Notice

Aluminum HYREDUCER™, 3.25 in L, Hot Tin Dipped, #1 (19 STR) AWG (Barrel A), #2 (7 STR) AWG (Barrel B)



## Product Details

### General

Color Code	Orange; Tan
Connector Type	Reducer
Die Index	14;296
Material	Aluminum
Plating Type	Tin
Trade Name	HYREDUCER™
UPC	781810194683
UPC 12 Digit	7818101946833

### Dimensions

Dimension - B Length fraction	1-7/20 in
Dimension - B Length inch	1.35 in
Dimension - Length Overall inch	3.25 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Strip Length inch	1-7/16 in

### Conductor Related

Conductor - AL Str Size A	#1 (19 STR) AWG
Conductor - AL Str Size B	#2 (7 STR) AWG
Conductor - Copper Str Size A	#1 (19 STR) AWG
Conductor - Copper Str Size B	#2 (7 STR) AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)