



by Burndy Catalog ID: YRB28U26

Prop 65 Notice

Al Compression reducing splice tubing, 4/0 str(Barrel A), 2/0 str(Barrel B), 600V-35KV, Tin plated, White, 298 index.

Used within underground systems



Product Details

General

Application	FOR ALUMINUM TO COPPER AND ALUMINUM TO ALUMINUM	
Color Code	White	
Connector Type	Reducer	
Die Index	298	
Feature - Barrel Style	Chamfered	
Material	Aluminum	
Physical Attribute - Number of Crimps Required	2	
Plated	Y	
Plating Type	Tin - Electro Plated	
Sub Brand	REDUCER SPLICES, HYREDUCER	
Temperature Rating	194	
Trade Name	HYREDUCER™	
Туре	Type YRB	
UPC	781810739334	
UPC 12 Digit	7818107393344	

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.36 in
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.31 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-7/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size A 4/0 AWG

Conductor - AL Str Size A Range	4/0 AWG
Conductor - AL Str Size B	2/0 AWG
Conductor - AL Str Size B Range	2/0 AWG
Conductor - Copper Str Size	4/0
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size A Range	4/0 AWG
Conductor - Copper Str Size B	2/0 AWG
Conductor - Copper Str Size B Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

	ck Quantity	1	
--	-------------	---	--

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)