

YRB31U31TW

by Burndy
Catalog ID: YRB31U31TW

Prop 65 Notice

Al Hyreducer Splice, 5.43" L, 350 kcmil(Al/Cu)(Barrel A), 350 kcmil(Al/Cu)(Barrel B), Hot Tin Dipped Plating, Brown, 299 Index, For Al to Al&Al to Cu



Product Details

General

Color Code	Brown
Connector Type	Reducer
Die Index	299
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192726

Dimensions

Dimension - B Length fraction	2-17/50 in
Dimension - B Length inch	2.34 in
Dimension - Length Overall inch	5.43 in
Dimension - Strip Length inch	2.5 in

Conductor Related

Conductor - AL Str Size A	350 kcmil
Conductor - AL Str Size B	350 kcmil
Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)