

YRB3934TW

by Burndy
Catalog ID: YRB3934TW

Prop 65 Notice

HYREDUCER™-750/500, 4.75 in long



Product Details

General

Color Code	Black
Die Index	24
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192900

Dimensions

Dimension - B Length inch	2.06 in
Dimension - Length BB inch	2.06 in
Dimension - Length Overall inch	4.75 in
Dimension - Outside Diameter inch	1.30 in

Conductor Related

Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)