



YRV8CV10L

by Burndy
Catalog ID: YRV8CV10L

Cu Reducer Butt Splice, W/InspWindow, Barrel X:8 Barrel Y:10-12 , 1.15" L, Tin Plated.

Features: The HYREDUCER Is A Connector For Splicing Two Different Size Wires, The Larger Conductor Is Inserted First And Butts Against The Center Of The Connector Where The Smaller Barrel Begins, Constructed Of Pure Electrolytic Copper Tubing For Maximum Conductivity, Tin Plated To Resist Corrosion, The HYREDUCER Accommodates A Wide Range Of Cable Sizes, Wire Strip Length: Side A: 0.44 IN, Side B: 0.53 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Side A And B: Y8MRB-1, MR20, MR8G98, MR8-9Q Tool

Product Details

General

Application	For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)
Connector Type	Reducer
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810026380

Dimensions

Dimension - A Outside Diameter inch	0.27 in
Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - B Outside Diameter inch	0.21 in
Dimension - Length BB inch	0.53 in
Dimension - Length Overall inch	1.15 in
Length	1.15 in

Conductor Related

Conductor - Copper Flex H Size B Range	N/A
Conductor - Copper Str Size	8
Conductor - Copper Str Size B	10
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)