



## YRV8CV14L

by Burndy  
Catalog ID: YRV8CV14L

Cu Reducer Butt Splice, W/InspWindow, Barrel A:8 Barrel C:14 (Str), 1.16" L, Tin Plated, For Aircraft Applications.

Features: Cu Reducer Butt Splice, with Insp Window, 1.16 IN L, Tin Plated

## Product Details

### General

Application	For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)
Connector Type	Reducer
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810035924

### Dimensions

Dimension - A Outside Diameter inch	0.27 in
Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.49 in
Dimension - B Outside Diameter inch	0.16 in
Dimension - Length BB inch	0.39 in
Dimension - Length Overall inch	1.16 in
Length	1.16 in

### Conductor Related

Conductor - Copper Flex H Size B Range	N/A
Conductor - Copper Str Size	8
Conductor - Copper Str Size B	14
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)