

YS1CLBOX

by Burndy
Catalog ID: YS1CLBOX

Prop 65 Notice

Compression CU Reducer/Splice, 1(Str) 75(Navy), 600V-35kV, Standard Barrel, Tin Plated.

Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Color Code: Green, Tapered End: No, Oil Stop: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Die Index: 11 Or 375, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y2MR, Y1MRTC Tool, Y1MRTC Die, (2), MD7-34R Tool, W1CVT Die, (1), MD6, OUR840 Tool, X1CRT Die, (1), Y35, Y39, Y750 Tool, U1CRT-1 Die, (1), Y46 Tool, U1CRT-1 Die With PUADP-1 Adapter, (1), Wire Strip Length: 15/16 IN, Conductor Type: Commercial Stranded Copper



Product Details

General

Application	For Limited Space Applications
Color Code	Green
Connector Type	Splice
Die Index	11;98;375
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810555002
UPC 12 Digit	7818105550022

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Strip Length inch	15/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Size	1 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)