

## YS25PULL

by Burndy  
Catalog ID: YS25PULL

Hylink Cu compression long barrel code splice tubing, Beveled entry, 1/0 STR kcmil.Cu, 600V-35KV, Tin plated, Pink, 12 or 348 Index.

Features: Long barrel length, Four center conductor stops, High pull out force



## Product Details

### General

|                        |                |
|------------------------|----------------|
| Application            | Splice         |
| Color Code             | Pink           |
| Connector Type         | Splice         |
| Die Index              | 12             |
| Feature - Barrel Style | Chamfered      |
| Feature - Barrel Type  | Long           |
| Material               | Copper         |
| Plated                 | Y              |
| Plating Type           | Tin - Bright   |
| Sub Brand              | SPLICE, HYLINK |
| Trade Name             | HYLINK™        |
| Type                   | YS             |
| UPC                    | 781810105498   |
| UPC 12 Digit           | 7818101054988  |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 1.35 in |
| Dimension - L Length Overall mm | 78 mm   |
| Dimension - Length Overall inch | 3.08 in |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

### Conductor Related

|                             |     |
|-----------------------------|-----|
| Conductor - Copper Str Size | 1/0 |
|-----------------------------|-----|

## Certifications and Compliance

|                                    |              |
|------------------------------------|--------------|
| Certification - CSA Approved       | No           |
| Certification - ETL                | No           |
| Certification - UL Recognized      | No           |
| Certification - cULus              | No           |
| Industry Standard(s)               | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM           |
| UL Listed                          | No           |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)