

YS26LBOX

by Burndy
Catalog ID: YS26LBOX

Prop 65 Notice

Copper Compression Splice, 2/0 AWG, 2.17" Splice Length, Short Barrel, Tin Plated.

Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Tapered End: No, Oil Stop: No, Color Code: Black, Die Index: 13 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W26VT Die, (2), MD6, OUR840 Tool, X26RT Die, (2), Y35, Y39, Y750 Tool, U27RT-1 Die, (1), Y46 Tool, U27RT-1 Die With PUADP-1 Adapter, (1), Wire Strip Length: 1 IN, Conductor Type: Commercial Stranded Copper



Product Details

General

Application	For Limited Space Applications
Color Code	Black
Connector Type	Splice
Die Index	13;100
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810556252
UPC 12 Digit	7818105562522

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - L Length Overall mm	55 mm
Dimension - Length Overall inch	2.17 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Strip Length inch	1 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)