



YS28AT

by Burndy
Catalog ID: YS28AT

Prop 65 Notice

Aluminum Compression Splice, 4/0 AWG, 5.05" Splice Length, Long Barrel, Tapered End, Tin Plated

Product Details

General

Color Code	White
Connector Type	Splice
Die Index	298
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810001394

Dimensions

Dimension - B Length inch	2.16 in
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.05 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Pad Width inch	2.42 in
Dimension - Strip Length inch	2 3/4

Conductor Related

Conductor - AL Str Size	4/0 AWG
-------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)