

# YS28UCG1

by Burndy  
Catalog ID: YS28UCG1

URD Insulator Splice Kit, 4/0 AWG Comp, 4/0 Str Al, 4/0 AWG (6-1)  
ACSR, 4/0 Str Cu, 600 V



## Product Details

### General

|                 |               |
|-----------------|---------------|
| Connector Type  | Splice        |
| Die Index       | 249;840       |
| Insulation      | Y             |
| Insulation Type | Diaform       |
| Material        | Aluminum      |
| Plated          | N             |
| Plating Type    | Unplated      |
| UPC             | 781810187906  |
| UPC 12 Digit    | 7818101879066 |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 1.9 in  |
| Dimension - Length Overall inch | 4.12 in |

### Conductor Related

|                                     |                       |
|-------------------------------------|-----------------------|
| Conductor - ACSR Str Size A         | 4/0 (6/1) Penquin AWG |
| Conductor - ACSR Str Size A Range   | 4/0 (6/1) Penquin AWG |
| Conductor - ACSR Str Size B         | 4/0 (6/1) Penquin AWG |
| Conductor - ACSR Str Size B Range   | 4/0 (6/1) Penquin AWG |
| Conductor - AL Str Size A           | 4/0 AWG               |
| Conductor - AL Str Size A Range     | 4/0 AWG               |
| Conductor - AL Str Size B           | 4/0 AWG               |
| Conductor - AL Str Size B Range     | 4/0 AWG               |
| Conductor - Copper Str Size A       | 4/0 AWG               |
| Conductor - Copper Str Size A Range | 4/0 AWG               |
| Conductor - Copper Str Size B       | 4/0 AWG               |
| Conductor - Copper Str Size B Range | 4/0 AWG               |

### Certifications and Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |

|                                    |    |
|------------------------------------|----|
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)