

## YS2CPULL

by Burndy  
Catalog ID: YS2CPULL

Hylink Cu compression long barrel code splice tubing, Beveled entry, #2 STR kcmil.Cu, 600V-35KV, Tin plated, Brown, 10 Index.

Features: Long barrel length, Four center conductor stops, High pull out force



## Product Details

### General

Application	For heavy duty applications
Color Code	Brown
Connector Type	Splice
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	Type YS
UPC	781810090190
UPC 12 Digit	7818100901900

### Dimensions

Dimension - B Length inch	1.22 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.82 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	2 AWG
-----------------------------	-------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)