



YS30AT

by Burndy
Catalog ID: YS30AT

Prop 65 Notice

Al Compression Splice, 300 Kcmil, 5.91 IN L, Tin Plated, 470 Index

Product Details

General

Color Code	Blue
Connector Type	Splice
Die Index	470
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Insulation	Y
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810094372

Dimensions

Dimension - B Length inch	2.54 in
Dimension - Inside Diameter inch	0.65 in
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.91 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Strip Length inch	3 1/8

Conductor Related

Conductor - AL Str Size	300 kcmil
-------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)