



# YS34AT

by Burndy  
Catalog ID: YS34AT

Prop 65 Notice

High Voltage Uninsulated Al Tube Compression Splice, 500 kcmil Al Cable, 7.79" L

## Product Details

### General

|                                                |                      |
|------------------------------------------------|----------------------|
| Color Code                                     | Pink                 |
| Connector Type                                 | Splice               |
| Die Index                                      | 300                  |
| Feature - Barrel Style                         | Tapered              |
| Feature - Barrel Type                          | Standard             |
| Material                                       | Aluminum             |
| Physical Attribute - Number of Crimps Required | 6                    |
| Plated                                         | Y                    |
| Plating Type                                   | Tin - Electro Plated |
| Trade Name                                     | HYLINK™              |
| UPC                                            | 781810757611         |

### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - B Length inch         | 3.39 in |
| Dimension - L Length Overall mm   | 198 mm  |
| Dimension - Length Overall inch   | 7.79 in |
| Dimension - Outside Diameter inch | 1.32 in |
| Dimension - Pad Width inch        | 3.79 in |
| Dimension - Strip Length inch     | 4 1/8   |

### Conductor Related

|                         |           |
|-------------------------|-----------|
| Conductor - AL Str Size | 500 kcmil |
|-------------------------|-----------|

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)