



YS39AG7

by Burndy
Catalog ID: YS39AG7

Prop 65 Notice

Aluminum Compression Splice, 750 kcmil, 6.64" Splice Length, Long Barrel, Tin Plated.

Product Details

General

Connector Type	Splice
Die Index	608;786
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810102619
UPC 12 Digit	7818101026199

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.52 in
Dimension - L Length Overall mm	169 mm
Dimension - Length Overall inch	6.64 in
Dimension - Outside Diameter inch	1.50 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)