

YSA321R2N

by Burndy
Catalog ID: YSA321R2N

Prop 65 Notice

DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).



Product Details

General

Connector Type	Terminal
Die Index	317;M
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810017135
UPC 12 Digit	7818100171355

Dimensions

Dimension - B Length inch	3.06 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.71 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.90 in
Dimension - Thread Size	1/2
Thickness - Pad	0.38 in

Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	350 kcmil
Conductor - Copper Str Size	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

3

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)