



YSCM231

by Burndy
Catalog ID: YSCM231

Prop 65 Notice

Colour coded uninsulated YSCM seamless parallel splice connectors, Beveled entry, 230800(Min), 230800(Max), Up to 600V, Tin plated, Brown, 16 Index.

Features:Colour coded uninsulated YSCM seamless parallel splice connectors,Tin plated, Brown, 16 Index

Product Details

General

Application	Type YSCM HYLINK seamless parallel splice connectors permit stranded wires to be laid parallel inside the connector and spliced together with BURNDY compression tools
Color Code	Yellow
Connector Type	Splice
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	Type YSCM
UPC	781810363287
UPC 12 Digit	7818103632877

Dimensions

Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.05 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Strip Length inch	1-1/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000 V

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)