

YSD26R2R

by Burndy
Catalog ID: YSD26R2R

Prop 65 Notice

Aluminum compression sleeve with solid center barrier. Designed for commercial and heavy residential services, Installed with standard tooling



Product Details

General

Color Code - Side A	Gray
Color Code - Side B	Red
Die Index	249;K-840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810144008
UPC 12 Digit	7818101440088

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B	4/0 AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size B	2 AWG, 3 AWG, 4 AWG
Conductor - AL Str Size B Range	2 AWG-4 AWG
Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	2 AWG, 3 AWG, 4 AWG
Conductor - Copper Str Size B Range	2 AWG-4 Awg

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)