

YSD27R25R

by Burndy
Catalog ID: YSD27R25R

Prop 65 Notice

AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Black (Side A), Yellow (Side B)



Product Details

General

Color Code - Side A	Black
Color Code - Side B	Yellow
Die Index	249;K-840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810145104
UPC 12 Digit	7818101451044

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	3/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	3/0 AWG
Conductor - Copper Str Size B	1/ AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)