



YSE14H

by Burndy
Catalog ID: YSE14H

Prop 65 Notice

600 VOLTS, 105° C.

Features: The Types YSE And YSE-H INSULINKS Are High Quality Nylon Insulated Butt Splices Designed For Splicing Aircraft And Commercial Flexible Cables, Manufactured From Tin Plated, Seamless Electrolytic Copper Tubing With Integral Barrel/Insulation Grip: Provides Maximum Conductivity And Tensile Strength, Plus Excellent Cable Support And Strain Relief, Split Heavy Wall Insulation Grip: Provides Stronger Insulation Grip And Strain Relief, Smooth Funnel Entry: Provides Easy Wire Insertion, Transparent Nylon Insulation: Permits Easy Wire Inspection, Insulation Support: No, Installation Tool: Y10D Tool, Ratchet: MR8-33S-1 Tool, Conductor Type: Commercial/Aircraft Stranded Copper, Wire Strip Length: 11/32 IN, Color Code: Blue

Product Details

General

Application	For Splicing Aircraft And Commercial Flexible Cables
Color Code	Blue
Connector Type	Splice
Construction Material - Main	Copper
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	YSE-H
UPC	781810803868
UPC 12 Digit	7818108038688

Dimensions

Dimension - B Length fraction	3/13 in
Dimension - B Length inch	0.23 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - Length Overall inch	1.36 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Strip Length inch	11/32

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor - Copper Str Size	16;14
Conductor - Copper Str Size Range	16-14
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)