

YSES14K

by Burndy
Catalog ID: YSES14K

Prop 65 Notice

RADIATION RESISTANT INSULATED BUTT SPLICE, POLYVINYLDENE FLOURIDE (PVF2) INSULATED.



Product Details

General

Color Code	Blue
Connector Type	Splice
Insulation	Y
Insulation Type	Kynar
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	150
Trade Name	INSULINK™
Type	Radiation Resistant KYNAR Splice
UPC	781810085776
UPC 12 Digit	7818100857766

Dimensions

Cable Insulation Diameter Maximum	0.153 in
Dimension - B Length fraction	15/79 in
Dimension - B Length inch	0.19 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.25 in
Dimension - P inch	0.04 in
Dimension - Pad Width inch	0.15 in
Dimension - Strip Length inch	3/16 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	16;15;14
Conductor - Copper Solid Size Range	16-14

Conductor - Copper Str Aircraft Size	AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor - Copper Str Size	16;14
Conductor - Copper Str Size Range	16-14
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)